



iCountLaserCM20

Portable Particle Monitor



A 2-minute contamination test procedure:

A portable particle monitor designed to be used in the field

icountLCM20 is a proven answer to fluid system contamination monitoring offering a 2-minute test procedure. Multi-standard ISO, NAS, AS4059E and GOST 17216 cleanliness reporting, data entry, data graphing and integral printing are all standard on this world proven contamination monitor.

Product Features:

- icountLCM20 is a proven answer to fluid system contamination monitoring.
- 2-minute test procedure.
- Multi-standard ISO, NAS, AS4059E and GOST 17216 cleanliness reporting.
- Data entry, data graphing and integral printer.
- 420 bar rated maximum pressure.
- Supported by the offline UBS and online SPS accessories.



Technical specifications – LCM 20

Feature	Specification
Principle of operation	Optical scanning analysis and measurement of actual particulates
Fluid compatibility	Mineral oil and petroleum-based fluids. For other fluids consult Parker
Test time	2 minutes; repeat test time every 2 minutes
Particle counts	MTD >4, >6, >14, >21, >38 and >70e ⁱ µm ACFTD >2, >5, >10 ⁱⁱ , >15, >25, >50 and >100e ⁱ µm
Analysis range ⁱⁱⁱ	ISO 4406: 7 to 22 inclusive; NAS 1638: 0 to 12 inclusive; AS4059E[cum]: 000 to 12 inclusive; AS4059E[diff]: 00 to 12 inclusive; GOST 17216: 00–17 inclusive;
Repeatability ^{iv}	≤7% of measured counts for MTD Particle Sizes: 4, 6, 14µm
Coincidence Error Limit ^v	23,000 particles / mL
Data entry	32-character two-line dot-matrix LCD. Full alphanumeric entry facility on keypad
Calibration	The LCM and calibration master sample the same particle distribution suspension. The LCM is calibrated to the master to meet specification at the measured points. MTD – instrument calibrated using MTD reference material. ACFTD – instrument calibrated using ACFTD reference material. Consult Parker for recalibration.
Certification	This product complies with all relevant EU declarations of conformity
Working Viscosity	2–100 centistokes (500 cSt with Single Point Sampler)
CMP Max. Viscosity Range	200 Centistokes (100 cSt when reporting in GOST standard and using Heated Bath)
Oil temp. range	+5°C to +80°C
Operating temp. range	+5°C to +40°C
Max. working pressure	2.5 bar when using Case Mounted Pump; up to 420 bar when CMP not used
Max. flow rate	30ml/min when using Case Mounted Pump. System 20 Sensors flow up to 400 l/min. Single Point Sampler can be used for high flow. (Consult Parker)
System connection	Via System 20 In-line Sensors or the Single Point Sampler
Memory store	300 test (scrolling memory) capacity
Integral printer	16-column printer for hard copy data
Computer compatibility	Interface via RS232 connection at 9600 baud rate
Power	Replaceable battery pack: Requires 6 x 1.5V D cells. Rechargeable battery pack: Supply voltage of 12V DC 1A max, 9mm jack plug with positive centre contact. Unit: Supply voltage 12V DC 3A max, 9mm jack plug with positive centre contact.
Battery performance	Replaceable battery pack: maximum 25 tests before replacement Rechargeable battery pack: maximum 40 tests before recharging
Fuse	1.25A fast blow fuse included for overload protection (spare supplied)
icountLCM20 cover	Weatherproof cover
Construction	Case: ABS Hand-held display: ABS Keypad: Fluorosilicone rubber Carrying case: Astraboard Mechanical components: Brass, plated steel, stainless steel and aluminium Seals: FKM (Viton). Other materials available - consult Parker Hoses: Nylon (Kevlar braided microbore). Stainless steel armoured ends
Hose length	Fluid connection hose: 1.2 metres (1 metre extensions can be used) Hand-held display cable length: 1 metre. CMP standard hose length: 0.26 metre
Portability	icountLCM20, 8kg; LCM with CMP 8.15kg. Carrying case 5kg approx.
Commissioning kit	6-off D cell batteries; 1-off print rolls (shrink wrapped); 2-off printer ribbons; 'ParSmart Downloader' software plus cable; weather protector cover; 12V DC power supply; Rechargeable battery pack

i The number of particles >70 µm (MTD), >100 µm (ACFTD) and in the ranges 50–100 µm and 100–200 µm (GOST) are not measured by this device. However, estimated values (indicated by the letter e on the display) have been calculated using the following formulae: MTD: >70e µm = >38 µm × 0.06816; ACFTD: >100e µm = >50 µm × 0.06816; GOST: 50–100e µm = >50 µm (ACFTD) × 0.93184; GOST: 100–200e µm = >50 µm (ACFTD) × 0.06816

ii Special versions only - consult Parker.

iii The instrument only uses the shorthand in these standards for reporting contamination levels.

iv 95% confidence level using an MTD distribution with a concentration of 6mg/L.

v ISO 11171:2016 Annex B methodologies followed to determine Coincidence Error Limits

Features & Benefits

- Special 'diagnostics' are incorporated into the iCountLaserCM microprocessor control to ensure effective testing.
- Routine contamination monitoring of oil systems with iCountLaserCM saves time and saves money.
- Contamination monitoring is now possible during application operation - iCountLaserCM saves on production downtime.
- Data entry allows individual equipment test log details to be recorded.
- Data retrieval of test results from memory via hand set display.
- Automatic test cycle logging of up to 300 tests can be selected via hand set display.
- Totally portable, can be used as easily in the field as in the laboratory.
- Automatic calibration reminder.
- Instant, accurate results achieved with a 2 minute test cycle.
- Data entry allows individual equipment footprint record.
- Data graphing selectable via the integral printer.
- Auto 300-test cycle logging via LCD handset input.
- RS232 to USB computer interface.
- Limit level output to control peripheral equipment such as off-line filtration via internal relay limit switches.
- Auto-testing allows for the conducting of automatic sequencing tests on flushing systems for example.
- Memory access gives test search facility
- Worldwide service and technical support.
- Re-calibration - Annual certification by an approved Parker Service Centre.

Typical Applications

- Construction machinery
- Industrial plant
- Hydraulic equipment & system manufacturers
- Research & testing institutes
- Offshore & power generation
- Marine
- Military equipment applications

Parker LaserCM Portable Particle Monitor

With 35 years' experience in manufacturing the world's best-selling portable contamination monitor - the progression to the iCountLaserCM with its opto-mechanical, continuous wave single point source laser (SPSL) is both a natural and a customer driven development.



Specification

Particle Contamination Monitors, have been widely used for many years in condition monitoring of hydraulic fluids.

However, it is only recently that PCM's have become flexible enough to enable the instruments to be taken out of the laboratory and used on-line in order to obtain the most credible form of results.

Unusually, the move from fixed laboratory use, to portable field use has not been at the expense of accuracy or user flexibility, but has actually enabled the instruments to be used over a wider range of applications and situations.

The most common monitoring technique used in PCM's is that of light obscuration or light blockage. Here, a focused light source is projected through a moving column of oil, (in which the contaminants being measured are contained), causing an image of the contaminant to be projected on to a photo diode cell, (changing light intensity to an electrical output).



The electrical output of the photo diode cell will vary in accordance with the size of the particles contained in the column of oil; the larger the particle, the bigger the change in the photo diode electrical output.


On-line PCM's must be able to test the oil sample at whatever cleanliness it is delivered to the machine. Parker therefore had to develop technology to ensure the on-line PCM was able to test a sample without the conventional laboratory technique which requires dilution - a practice that would have been simply impossible with a portable unit.

By careful design and window sizing, an ISO code 22 at >4 micron per 100 ml, (equivalent to up to 2.3 million particles >4 micron per 100 ml), can be achieved without making the instrument susceptible to counter saturation or coincidence error.

These high saturation point on-line PCM's, whilst losing none of the accuracy of their laboratory counterparts, enable particle counting to be carried out quickly and accurately.


How does icountLaserCM work?

- The icountLaserCM portable particle counter features microprocessor controlled optical scanning for accurate contaminant measurement with a calibration range from ISO 7 to ISO 22 with no counter saturation.
- The particles are measured by a photo diode that converts light intensity to a voltage output which is recorded against time.
 - As the particle moves across the window the amount of light lost is proportional to the size of the particle. This reduction in voltage is measured and recorded.
 - The electrical output of the photo diode cell will vary in accordance with the size of the particles contained in the column of oil; the larger the particle, the bigger the change in the photo diode electrical output.
 - This value is counted and stored in the icountLaserCM computer in one of 5 measured channels according to particle size.
 - Readouts are displayed on the hand-held LCD in the accepted ISO and NAS standards ready for hard copy printing or RS232 computer download.
 - The on-board computer allows storage of up to 300 test results.




Core technology that proves itself in icountLaserCM

The icountLaserCM Particle Contamination Monitor features microprocessor controlled optical scanning for accurate contaminant measurement with a calibration range from ISO 7 to ISO 22 with no counter saturation.



Commissioning Kit



Description	LaserCM (LCM20 20 22)	LaserCM (LCM20 20 62)
ABS structural foam and injection moulded case	•	•
ABS handheld display	•	•
Mechanical composition – Brass, plated steel, stainless steel and aluminium	•	•
Fluorocarbon seals	•	•
Perfluoroelastomer seals	•	•
Nylon hoses (kevlar braided microbore)	•	•
Stainless steel armoured hose ends	•	•
1.2m fluid connection hose	•	•
Rechargeable battery pack	•	•
12Vdc power supply	•	•
Fast blow fuse	•	•
Unique optical scanning system	•	•
Bonded glass optical window enclosed in SS plate	•	•
Micron channels analysis to 5 measured channels and the sixth channel is calculated.	•	•
Analysis range ISO 7 to 22 incl. (NAS 0 to 12)	•	•
32 character dot matrix LCD. Alpha numeric keypad	•	•
Data retrieval	•	•
Calibration - see note below	•	•
Viscosity range 2 to 100 cSt. 500 cSt. with SPS	•	•
Fluid temp.+5 to +80°C	•	•
Ambient temp.+5 to +40°C	•	•
2 minute test completion time	•	•
Memory store – 300 test memory	•	•
Battery operated 6 x 1.5 D cells	•	•
Phosphate Ester group compatibility	•	•
Mineral oil & petroleum based fluid compatibility	•	•
Up to 420 bar (6000 psi)	•	•
Integral 16 column printer	•	•
RS232 to USB computer interface	•	•
Astra board case weight – (Kg)	5	5
Unit weight – (Kg)	8	8
ParSmart software and cable link pack	•	•
Weather protector cover	•	•
CE certified	•	•
Auto logging	•	•

The LCM and calibration master sample the same particle distribution suspension. The LCM is calibrated to the master to meet specification at the measured points.

MTD – instrument calibrated using MTD reference material.

ACFTD – instrument calibrated using ACFTD reference material.

Consult Parker for recalibration.

Operation

Operating the Parker icountLaserCM is as simple as pressing the start button and turning the dial. The test procedure is automatic and in the case of the icountLaserCM takes no more than 2 minutes to complete.

icountLCM20 makes the difference in industry

The LCM20 is CE marked. icountLaserCM offers users advanced laser technology, a fast, dynamic and on-line 2 minute system test cycle. An icountLaserCM Aggressive Fluids model is also available, suitable for monitoring corrosive fluids such as phosphate ester based lubricants used in commercial aviation.

MTD calibration

The LCM and calibration master sample the same particle distribution suspension. The LCM is calibrated to the master to meet specification at the measured points.

MTD – instrument calibrated using MTD reference material.

Consult Parker for recalibration.

Switch On



Start Test



icountLaserCM20 Portable Particle Monitor

Why On-Site Fluid Contamination Monitoring?

- Certification of fluid cleanliness levels.
- Early warning instrument to help prevent catastrophic failure in critical systems.
- Immediate results with laboratory accuracy.
- To comply with customer cleanliness requirements and specifications.
- New equipment warranty compliance.
- New oil cleanliness testing.



Data Download Management

Dedicated software, provides the link between an icountLaserCM20 and your computer management system.



16-column printer for hard copy data. A feature of the icountLaserCM is the on-board printout data graphing option developed to support predictive maintenance procedures.

.....		Parker LCM20	
On Line		Test Number 016	
Date		D M Y	
Time		16/01/20	
ISO:		12:44	
20/19/15		NAS Class	
		11	
Counts/100ml			
4-6µ		471464	
NAS Class		---	
6-14µ		295014	
NAS Class		11	
14-21µ		19693	
NAS Class		9	
21-38µ		11300	
NAS Class		11	
38-70µ		342	
NAS Class		8	
70µ		22	
NAS Class		7	
Notes		Notes	

ISO 4406 reporting

Correlation to NAS 1638

Ordering Information

icountLaserCM and 'Classic' icountLaserCM



Standard products table

Part Number	Supersedes	Description
LCM202022	LCM20.2022	icountLCM20 (MTD calibrated)
ACC6NE015	B84702	Printer roll x 5
ACC6NE014	P.843702	Printer ribbon
ACC6NE013	B84609	Re-chargeable battery pack
ACC6ND002	P849603	Weather protector cover
ACC6ND000	B84703	USB to RS232 Download Cable

Note 1: Part numbers featured with bold highlighted codes will ensure a 'standard' product selection.

Note 2: Alternate displayed part number selection will require you to contact Parker Filtration for availability.

Product configurator

Model	Fluid type		Options	
LCM2020	2	Hydraulic mineral	1	icountLCM20 (ACFTD calibrated)
	6	Aggressive fluids	2	icountLCM20 (MTD calibrated)
			7	icountLCM20 with CMP (ACFTD calibrated)
			8	icountLCM20 with CMP (MTD calibrated)

Note 1: Part numbers featured with bold highlighted codes will ensure a 'standard' product selection.

Note 2: Alternate displayed part number selection will require you to contact Parker Filtration for availability.

Note 3: Option 7 and 8 with CMP (Case mounted pump).

Parker Worldwide

Europe, Middle East, Africa

AE – United Arab Emirates, Dubai
Tel: +971 4 8127100
parker.me@parker.com

AT – Austria, St. Florian
Tel: +43 (0)7224 66201
parker.austria@parker.com

AZ – Azerbaijan, Baku
Tel: +994 50 2233 458
parker.azerbaijan@parker.com

BE/NL/LU – Benelux, Hendrik Ido Ambacht
Tel: +31 (0)541 585 000
parker.nl@parker.com

BG – Bulgaria, Sofia
Tel: +359 2 980 1344
parker.bulgaria@parker.com

BY – Belarus, Minsk
Tel: +48 (0)22 573 24 00
parker.poland@parker.com

CH – Switzerland, Etoy
Tel: +41 (0)21 821 87 00
parker.switzerland@parker.com

CZ – Czech Republic, Klecany
Tel: +420 284 083 111
parker.czechrepublic@parker.com

DE – Germany, Kaarst
Tel: +49 (0)2131 4016 0
parker.germany@parker.com

DK – Denmark, Ballerup
Tel: +45 43 56 04 00
parker.denmark@parker.com

ES – Spain, Madrid
Tel: +34 902 330 001
parker.spain@parker.com

FI – Finland, Vantaa
Tel: +358 (0)20 753 2500
parker.finland@parker.com

FR – France, Contamine s/Arve
Tel: +33 (0)4 50 25 80 25
parker.france@parker.com

GR – Greece, Piraeus
Tel: +30 210 933 6450
parker.greece@parker.com

HU – Hungary, Budaörs
Tel: +36 23 885 470
parker.hungary@parker.com

IE – Ireland, Dublin
Tel: +353 (0)1 466 6370
parker.ireland@parker.com

IL – Israel
Tel: +39 02 45 19 21
parker.israel@parker.com

IT – Italy, Corsico (MI)
Tel: +39 02 45 19 21
parker.italy@parker.com

KZ – Kazakhstan, Almaty
Tel: +7 7273 561 000
parker.easteurope@parker.com

NO – Norway, Asker
Tel: +47 66 75 34 00
parker.norway@parker.com

PL – Poland, Warsaw
Tel: +48 (0)22 573 24 00
parker.poland@parker.com

PT – Portugal
Tel: +351 22 999 7360
parker.portugal@parker.com

RO – Romania, Bucharest
Tel: +40 21 252 1382
parker.romania@parker.com

RU – Russia, Moscow
Tel: +7 495 645-2156
parker.russia@parker.com

SE – Sweden, Borås
Tel: +46 (0)8 59 79 50 00
parker.sweden@parker.com

SK – Slovakia, Banská Bystrica
Tel: +421 484 162 252
parker.slovakia@parker.com

SL – Slovenia, Novo Mesto
Tel: +386 7 337 6650
parker.slovenia@parker.com

TR – Turkey, Istanbul
Tel: +90 216 4997081
parker.turkey@parker.com

UA – Ukraine, Kiev
Tel: +48 (0)22 573 24 00
parker.poland@parker.com

UK – United Kingdom, Warwick
Tel: +44 (0)1926 317 878
parker.uk@parker.com

ZA – South Africa, Kempton Park
Tel: +27 (0)11 961 0700
parker.southafrica@parker.com

North America

CA – Canada, Milton, Ontario
Tel: +1 905 693 3000

US – USA, Cleveland
Tel: +1 216 896 3000

Asia Pacific

AU – Australia, Castle Hill
Tel: +61 (0)2-9634 7777

CN – China, Shanghai
Tel: +86 21 2899 5000

HK – Hong Kong
Tel: +852 2428 8008

IN – India, Mumbai
Tel: +91 22 6513 7081-85

JP – Japan, Tokyo
Tel: +81 (0)3 6408 3901

KR – South Korea, Seoul
Tel: +82 2 559 0400

MY – Malaysia, Shah Alam
Tel: +60 3 7849 0800

NZ – New Zealand, Mt Wellington
Tel: +64 9 574 1744

SG – Singapore
Tel: +65 6887 6300

TH – Thailand, Bangkok
Tel: +662 186 7000

TW – Taiwan, Taipei
Tel: +886 2 2298 8987

South America

AR – Argentina, Buenos Aires
Tel: +54 3327 44 4129

BR – Brazil, Sao Jose dos Campos
Tel: +55 800 727 5374

CL – Chile, Santiago
Tel: +56 2 623 1216

MX – Mexico, Toluca
Tel: +52 72 2275 4200

EMEA Product Information Centre

Free phone: 00 800 27 27 5374

(from AT, BE, CH, CZ, DE, DK, EE, ES, FI, FR, IE, IL, IS, IT, LU, MT, NL, NO, PL, PT, RU, SE, SK, UK, ZA)

US Product Information Centre

Toll-free number: 1-800-27 27 537

www.parker.com