


# EnOxy 304

## Oxygen Membrane Module

Parker hollow-fibre membrane modules produce oxygen enriched air from compressed air to offer a cost effective, reliable and safe alternative to traditional oxygen gas supplies.

Parker modules can be built into a custom-made oxygen generator or can be integrated with your process to provide an on-demand, continuous source of oxygen gas.

Oxygen enriched air is used in many health and wellness related applications such as nitrox diving, oxygen bars and oxygen training rooms.



### Benefits:

- **Less membrane modules needed per enrichment system**  
More enriched air per fibre is produced from Parker hollow-fibre membranes than any other in the world
- **Use of low pressure standard industrial compressor**  
No high pressure compressor needed to obtain required enriched-oxygen flow
- **Energy savings**  
Operation at a low pressure requires less energy
- **Reduced CO<sub>2</sub> emissions**  
No heater required to open polymer membrane structure, thus reducing the energy consumption
- **Robust fibre**  
Most tolerant fibre to particle contamination
- **Large membrane diameter**  
Lowest membrane module pressure drop
- **Factory membrane ageing, pre-delivery**  
No performance decrease over time due to fibre ageing
- **Quick start-up time**  
Required enriched-oxygen purity is produced instantly, no time needed to heat-up
- **Flexible mounting arrangements**  
Can be mounted horizontal or vertical
- **Low noise operation**  
Radiated noise generated by membrane technology is extremely low
- **No maintenance required**  
No user serviceable parts
- **Small system footprint**  
Less modules needed to produce oxygen enriched air requirements

## Performance data

Standard test criteria are at 7 bar g, other specification points are an indication

Oxygen purity %	Minimum enriched oxygen flow rate in l/min <sup>1</sup>						
	28	30	32	34	36	38	40
4 bar g	16.9	17.3	17.7	18.1	18.4	18.8	-
5 bar g	21.5	22	22.5	23.0	23.5	24.0	24.5
6 bar g	26.3	26.9	27.5	28.1	28.7	29.3	29.9
7 bar g	31.1	31.9	32.6	33.3	34.0	34.7	35.4
8 bar g	36.1	37.0	37.8	38.6	39.4	40.2	41.1
9 bar g	41.3	42.2	43.1	44.1	45.0	45.9	46.9
10 bar g	46.5	47.5	48.6	49.7	50.7	51.8	52.8
11 bar g	51.9	53	54.2	55.4	56.6	57.8	58.9
12 bar g	57.3	58.6	59.9	61.3	62.6	63.9	65.2

Enriched oxygen flow exits at atmospheric pressure  
 Maximum pressure drop over nitrogen enriched flow <0.3 bar.  
 Maximum enriched oxygen flow rate = minimum flow rate + 30%  
<sup>1</sup> l/min refers to conditions at 1013 mbar(a) and 20°C

Oxygen purity %	Feed-air consumption at minimum enriched oxygen flow rate in l/min <sup>1</sup>						
	28	30	32	34	36	38	40
4 bar g	24.5	28.4	33.4	41.3	54.2	77.1	-
5 bar g	31.2	35.5	41.1	49.5	61.7	80.6	139
6 bar g	38.1	43.3	50.2	58.1	72.8	92.2	138
7 bar g	45.1	51.2	59.5	68.8	83.1	104	149
8 bar g	52.4	59.4	69.0	79.9	96.5	120	166
9 bar g	59.8	67.8	78.8	91.2	111	137	187
10 bar g	67.4	76.6	88.8	103	125	158	219
11 bar g	75.7	85.7	99.6	116	143	182	261
12 bar g	83.7	95.0	110	129	160	208	310

## Ambient Conditions

Ambient temperature	+2°C to +45°C*
Ambient pressure	atmospheric
Air quality	clean air without contaminants

\*Maximum inlet temperature, 35°C when operating at 13 bar g.

## Material applicable for EnOxy 304, 604 606

Housing	Steel
Tube	Aluminium
Coating (housing)	ESPC to Ral 7035 (Light Grey)
Coating (tube)	None

## Feed-air Conditions

Maximum operating pressure	13 bar g**
Min. / Max. operating temperature	+2°C / +45°C*
Maximum oil vapour content	<0.01 mg/m <sup>3</sup>
Particles	filtered at 0.01 µm cut off
Relative humidity	<100% (non condensing)

\*Maximum inlet temperature, 35°C when operating at 13 bar g.

\*\*Maximum inlet pressure, 10 bar g when operating at 45°C.

## Weight, Dimensions and Connections

Dimensions H x W x D	386 x 80 x 63 mm
Weight	2.3 kg
Connection feed-air	G <sup>3</sup> / <sub>8</sub> " female to ISO 228
Connection nitrogen enriched air	G <sup>3</sup> / <sub>8</sub> " female to ISO 228
Connection oxygen enriched air at atmospheric pressure	G <sup>3</sup> / <sub>8</sub> " female to ISO 228
Dimensional drawing	Refer to K3.1.348

## Flow Rate Corrections

Nitrogen flow rate at feed temperatures other than 20°C	Use bulletin S3.1.085*
Feed-air consumption at feed-air temperatures other than 20°C	Use bulletin S3.1.085*

\*version number may vary, make sure to use the most recent version.

## Note

Parker membrane systems produce both nitrogen and oxygen enriched air. Nitrogen enriched air can cause suffocation and oxygen enriched air causes increased fire hazards. The oxygen enriched air is available at ambient pressure and pressure build-up of enriched oxygen at the outlet must be prevented, otherwise a serious (reversible) decrease in performance will result. The nitrogen enriched air produced should be treated as pressurised air.

For more information please contact your local sales office or visit [www.parker.com/gsf](http://www.parker.com/gsf)

Parker has a continuous policy of product development and although the company reserves the right to changes specifications, it attempts to keep customers informed of any alterations.

©2023 Parker Hannifin Corporation. All rights reserved.

Catalogue: S3.1.0771 01/23

### EMEA Product Information Centre

Free phone: 00 800 27 27 5374

(from AT, BE, CH, CZ, DE, DK, EE, ES, FI, FR, IE, IL, IS, IT, LU, MT, NL, NO, PL, PT, RU, SE, SK, UK, ZA)

### US Product Information Centre

Toll-free number: 1-800-27 27 537

[www.parker.com/gsf](http://www.parker.com/gsf)

