

# SmartFluxx SA15020

Nitrogen membrane module

Parker hollow-fibre membrane modules produce nitrogen gas from compressed air to offer a cost-effective, reliable and safe alternative to traditional cylinder or liquid nitrogen gas supplies.

Nitrogen is used as a clean, dry, inert gas primarily for removing oxygen from products and/or processes.

Parker modules can be built into a custom-made nitrogen generator or can be integrated with your process to provide an on-demand, continuous source of nitrogen gas. Gas which can be used in a wide range of industries including food, beverage, pharmaceutical, laboratory, chemical, heat treatment, electronics, transportation, oil & gas, mining and marine.



## Benefits:

- **Less membrane modules needed per nitrogen system**  
More nitrogen per fibre is produced from Parker hollow-fibre membranes than any other in the world
- **Use of low pressure standard industrial compressor**  
No high pressure compressor needed to obtain required nitrogen flow
- **Energy savings**  
Operation at a low pressure requires less energy
- **Reduced CO<sub>2</sub> emissions**  
No heater required to open polymer membrane structure, thus reducing the energy consumption
- **Robust fibre**  
Most tolerant fibre to particle contamination
- **Large membrane diameter**  
Lowest membrane module pressure drop
- **Strong engineering plastic**  
Life-expectancy of more than 10 years
- **Factory membrane ageing, pre-delivery**  
No performance decrease over time due to fibre ageing
- **Quick start-up time**  
Required nitrogen purity is produced instantly, no time needed to heat-up
- **Flexible mounting arrangements**  
Can be mounted horizontal or vertical
- **Low noise operation**  
Radiated noise generated by membrane technology is extremely low
- **No maintenance required**  
No user serviceable parts
- **Small system footprint**  
Less modules needed to produce nitrogen requirements



ENGINEERING YOUR SUCCESS.

## Performance data

Purity %	Typical <sup>1)</sup> Nitrogen flow rate in m <sup>3</sup> /hr <sup>2)</sup>					
	99.5	99.0	98.0	97.0	96.0	95.0
<b>4 bar g</b> (58 psi g)	17 (10)	25 (15)	36 (21)	47 (28)	57 (34)	70 (41)
<b>5 bar g</b> (72.5 psi g)	23 (14)	33 (19)	49 (29)	66 (39)	82 (48)	93 (55)
<b>6 bar g</b> (87 psi g)	29 (17)	43 (25)	63 (37)	83 (49)	102 (60)	120 (71)
<b>7 bar g</b> (101.5 psi g)	37 (22)	53 (31)	78 (46)	100 (59)	125 (74)	154 (91)
<b>8 bar g</b> (116 psi g)	44 (26)	62 (36)	90 (53)	117 (69)	144 (85)	178 (105)
<b>9 bar g</b> (130.5 psi g)	49 (29)	72 (42)	103 (61)	133 (78)	165 (97)	216 (127)

Purity %	Typical Feed-air consumption at nitrogen flow rate in m <sup>3</sup> /hr <sup>2)</sup>					
	99.5	99.0	98.0	97.0	96.0	95.0
<b>4 bar g</b> (58 psi g)	127 (75)	126 (74)	135 (79)	145 (85)	155 (91)	169 (99)
<b>5 bar g</b> (72.5 psi g)	144 (85)	155 (91)	171 (101)	194 (114)	216 (127)	218 (128)
<b>6 bar g</b> (87 psi g)	170 (100)	191 (112)	214 (126)	239 (141)	261 (154)	276 (162)
<b>7 bar g</b> (101.5 psi g)	202 (119)	223 (131)	258 (152)	281 (165)	315 (185)	348 (205)
<b>8 bar g</b> (116 psi g)	232 (137)	255 (150)	293 (172)	323 (190)	361 (212)	399 (235)
<b>9 bar g</b> (130.5 psi g)	264 (155)	298 (175)	335 (197)	369 (217)	413 (243)	485 (285)

Maximum pressure drop at Purity: ≤0.2 bar

Values between brackets are indicative imperial values\*

<sup>1)</sup>The above data represents the typical performance of a single membrane module. Actual performance can vary depending on factors such as feed air pressure and temperature.

Please contact your Parker go to person for actual performance information to meet your application's requirements.

<sup>2)</sup>m<sup>3</sup>/hr refers to conditions at 1013 mbar(a) and 20°C

For higher purities please contact Parker

## Ambient Conditions

<b>Ambient temperature</b>	+2°C to +50°C (+36°F to 122°F)
<b>Ambient pressure</b>	atmospheric
<b>Air quality</b>	clean air without contaminants

## Mechanical Design Housing

<b>Design pressure</b>	14 bar g <sup>4</sup> (203 psi g <sup>4</sup> )
<b>Design temperature</b>	65°C <sup>4</sup> (149°F <sup>4</sup> )

<sup>4)</sup>Membrane operating limits are lower

## Operating Conditions Feed-air

<b>Maximum operating pressure</b>	9.0 bar g (130.5 psi g)
<b>Min. / Max. operating temperature</b>	+2°C to +50°C (+36°F to 122°F)
<b>Maximum oil vapour content</b>	<0.01 mg/m <sup>3</sup> (<0.01 ppm (w))
<b>Particles</b>	filtered at 0.01 µm cut off
<b>Relative humidity</b>	<100% (non condensing)

## Material

<b>Housing</b>	Aluminum
<b>Coating</b>	ESPC to RAL 7039 (Quartz Grey) Dry Film Thickness: 60 micron

## Services Available on Request

3D model CAD STEP file

## Flow Rate Corrections

<b>Nitrogen flow rate at feed-air temperatures other than 20°C</b>	Use bulletin S3.1.240 <sup>3</sup>
<b>Feed-air consumption at feed-air temperatures other than 20°C</b>	Use bulletin S3.1.240 <sup>3</sup>

<sup>3)</sup> Revision number may vary, make sure to use the most recent revision

## Weight, Dimensions and Connections

<b>Dimensions H x Ø D</b>	1740 x 280 mm (68.50" x 11.02")
<b>Weight</b>	46 kg (102 lb)
<b>Connection feed-air</b>	G 2 <sup>1</sup> / <sub>2</sub> " female to ISO 228
<b>Connection nitrogen enriched air</b>	G 2 <sup>1</sup> / <sub>2</sub> " female to ISO 228
<b>Connection oxygen enriched air at atmospheric pressure</b>	100mm (3.94") OD
<b>Dimensional drawing</b>	Refer to K3.1.339

## Note

Parker membrane systems produce both nitrogen and oxygen enriched air. Nitrogen enriched air can cause suffocation and oxygen enriched air causes increased fire hazards. The oxygen enriched air is available at ambient pressure and pressure build-up of enriched oxygen at the outlet must be prevented, otherwise a serious (reversible) decrease in performance will result. The nitrogen enriched air produced should be treated as pressurised air.

Parker has a continuous policy of product development and although the company reserves the right to change specifications, it attempts to keep customers informed of any alterations.

© 2019 Parker Hannifin Corporation. All rights reserved.

S3.1.244\_ENe

## EMEA Product Information Centre

Free phone: 00 800 27 27 5374

(from AT, BE, CH, CZ, DE, DK, EE, ES, FI, FR, IE, IL, IS, IT, LU, MT, NL, NO, PL, PT, RU, SE, SK, UK, ZA)

## US Product Information Centre

Toll-free number: 1-800-27 27 537

www.parker.com/gsf

ENGINEERING YOUR SUCCESS.

